

Free Standard Ground Shipping on Stock Springs for orders of \$40 or more in the Continental United States.

## REDUX™ Wave Spring Pricing

PRICE GROUP	QUANTITIES				PRICE GROUP	QUANTITIES			
	1-19 Each	20-49 Each	50-99 Each	100-199 Each		1-19 Each	20-49 Each	50-99 Each	100-199 Each
P1	4.90	3.06	2.21	1.52	P13	12.49	8.25	5.88	4.13
P2	5.23	3.54	2.53	1.75	P14	13.00	8.61	6.11	4.32
P3	5.55	3.75	2.67	1.89	P15	13.51	8.87	6.32	4.38
P4	6.26	4.24	2.99	2.11	P16	14.11	9.35	6.64	4.59
P5	6.85	4.60	3.29	2.33	P17	14.56	9.64	6.84	4.74
P6	7.16	4.73	3.36	2.37	P18	15.59	10.33	7.35	5.08
P7	7.81	5.24	3.72	2.63	P19	16.25	10.77	7.65	5.30
P8	8.99	6.12	4.39	3.05	P20	17.53	11.59	8.24	5.70
P9	9.31	6.37	4.53	3.19	P21	18.83	12.46	8.86	6.11
P10	10.15	6.94	4.95	3.48	P22	21.69	14.33	10.19	7.04
P11	10.54	7.17	5.10	3.60	P23	23.94	15.83	11.26	7.79
P12	11.64	7.65	5.46	3.82	P24	25.31	16.74	11.89	8.21

## Belleville Spring Washers Pricing

W1	7.53	4.70	2.46	1.43	W21	19.06	13.74	8.18	5.63
W2	7.52	4.88	2.56	1.48	W22	20.04	14.56	8.95	6.10
W3	7.90	5.17	2.68	1.57	W23	21.04	15.38	9.62	6.64
W4	8.33	5.47	2.84	1.66	W24	22.13	16.24	10.27	7.22
W5	8.75	5.89	3.01	1.83	W25	23.23	17.24	10.83	7.62
W6	9.18	6.18	3.19	1.92	W26	24.41	18.25	11.68	8.18
W7	9.69	6.54	3.41	2.03	W27	25.63	20.00	12.37	8.67
W8	10.16	6.93	3.63	2.14	W28	26.97	21.77	13.13	9.24
W9	10.65	7.29	3.83	2.29	W29	28.32	23.07	14.15	9.91
W10	11.21	7.73	4.11	2.49	W30	29.75	24.27	15.21	10.84
W11	11.77	8.11	4.37	2.62	W31	31.22	25.52	16.29	11.55
W12	12.30	8.52	4.56	2.76	W32	32.74	27.20	17.43	12.54
W13	12.93	8.95	4.84	2.96	W33	34.40	28.64	18.68	13.70
W14	13.54	9.41	5.12	3.19	W34	36.12	30.71	20.01	14.91
W15	14.23	9.86	5.44	3.42	W35	37.96	32.93	21.44	15.80
W16	14.96	10.58	5.79	3.74	W36	39.87	35.13	22.96	17.13
W17	15.70	11.11	6.18	3.96	W37	41.90	37.27	24.57	18.26
W18	16.50	11.72	6.59	4.27	W38	43.97	39.22	26.26	20.11
W19	17.29	12.40	6.97	4.71	W39	46.18	41.42	28.09	21.98
W20	18.15	13.03	7.51	5.15	W40	48.52	44.75	30.03	24.22

## LeeP™ Plastic Composite Spring Pricing

L1	12.47	10.48	8.89	8.02	L4	15.73	13.21	11.23	10.09
L2	13.46	11.30	9.63	8.66	L5	17.02	14.26	12.13	10.93
L3	14.56	12.21	10.40	9.37					

\* Type 302 may be substituted with Type 304 at Lee Spring's discretion. † Elgiloy is a trademark of Elgiloy Ltd. Partnership.



1. Select the spring you want by LEE STOCK NUMBER.
2. Read across to the last column PRICE GROUP to obtain the price code letter under either column M (Music Wire), column S (302\* Stainless Steel), or column S316 (316 Stainless Steel), or column E (Elgiloy®) where applicable.
3. Refer to the PRICE GROUP below for quantities up to 199 pieces of an item.
4. For pricing on HEFTY™ Die Springs and Constant Force Springs, refer to their specific product sections.
5. Prices are subject to change without notice. For pricing from 200 to 1000 pieces, or to place an order online, visit [www.lespring.com](http://www.lespring.com). For pricing above 1000 pieces, submit a request online at [www.lespring.com](http://www.lespring.com), call 888-777-4647, email [sales@lespring.com](mailto:sales@lespring.com), or fax a request to 888-426-6655.

**MAJOR CREDIT CARDS GLADLY ACCEPTED.**



**PRICES EFFECTIVE JANUARY 2024 • TERMS NET 30 DAYS.**

Prices Shown are Per Spring Per Quantity.

Quantities Cannot Be Combined to Lower Item Pricing.

**FREE GROUND SHIPPING AVAILABLE ON ORDERS OF \$40 OR MORE IN THE CONTINENTAL UNITED STATES.**

Stock Parts orders with a parts value below \$40.00 with delivery within the Continental United States will be charged freight, plus a \$20.00 handling charge. Stock Parts orders with delivery outside the Continental United States with a parts value more than \$40.00 will pay freight only and no handling charge.

PRICE GROUP	QUANTITIES			
	1-19 Each	20-49 Each	50-99 Each	100-199 Each
E	7.23	4.37	2.22	1.42
F	7.57	4.56	2.36	1.44
G	7.82	4.74	2.46	1.50
J	8.06	4.87	2.56	1.59
K	8.35	5.05	2.67	1.66
L	8.67	5.27	2.79	1.76
M	9.01	5.47	2.91	1.85
N	9.29	5.67	3.01	1.92
P	9.62	5.89	3.19	2.01
R	9.97	6.08	3.32	2.12
S	10.28	6.32	3.46	2.21
T	10.63	6.54	3.61	2.30
U	10.97	6.79	3.75	2.44
W	11.39	7.05	3.93	2.58
X	11.87	7.36	4.17	2.74
Y	12.24	7.61	4.33	2.85
Z	12.61	7.87	4.49	2.97
AA	12.99	8.13	4.68	3.10
AB	13.37	8.38	4.87	3.27
AC	13.78	8.65	5.05	3.43
AD	14.16	8.95	5.30	3.57
AE	14.56	9.23	5.49	3.75
AG	15.00	9.55	5.73	3.91
AJ	15.85	10.09	6.12	4.24
AK	16.30	10.46	6.41	4.44
AL	16.77	10.79	6.65	4.64
AM	17.22	11.13	6.94	4.87
AN	17.72	11.49	7.28	5.11
AO	18.20	11.85	7.54	5.35
AP	18.72	12.23	7.89	5.65
AR	19.23	12.64	8.21	5.90

PRICE GROUP	QUANTITIES			
	1-19 Each	20-49 Each	50-99 Each	100-199 Each
AS	19.78	13.06	8.59	6.20
AT	20.33	13.48	8.97	6.53
AU	20.89	13.95	9.39	6.87
AW	21.48	14.42	9.80	7.25
AX	22.10	14.90	10.27	7.61
AY	22.73	15.44	10.79	8.02
AZ	23.37	15.94	11.28	8.47
AZA	25.25	17.26	11.84	8.95
AZB	25.98	17.89	12.44	9.46
AZC	26.74	18.54	13.08	9.98
AZD	27.52	19.22	13.74	10.59
AZE	28.30	19.93	14.49	11.21
AZF	29.12	20.69	15.26	11.87
AZG	29.99	21.47	16.13	12.63
AZH	30.86	22.33	17.02	13.43
AZJ	31.77	23.20	17.98	14.29
AZK	32.70	24.15	19.01	15.25
AZL	33.69	25.14	20.18	16.26
AZM	35.33	26.32	21.40	17.37
AZN	36.40	27.44	22.79	18.61
AZO	37.48	28.65	24.22	19.96
AZP	38.55	29.95	25.83	21.44
AZQ	39.71	31.30	27.58	23.06
AZR	40.81	32.72	29.53	24.82
AZS	42.00	34.50	31.62	26.82
AZT	44.35	37.18	34.17	29.32
AZU	47.17	40.56	37.34	32.20
AZW	49.05	43.20	39.86	34.47
AZX	51.00	45.98	42.49	36.88
AZY	52.60	48.53	44.89	39.11
AZZ	54.55	51.47	47.68	41.67

When ordering, please specify suffix **M** for Music Wire, **S** for 302 Stainless Steel\*, **S316** for 316 Stainless Steel or **E** for Elgiloy, where applicable.